

3ft DisplayPort Panel Mount Cable - F/M

Product ID: DPPNLFM3



This 3ft panel mount DisplayPort cable features a DisplayPort male connector on one end, and a DisplayPort panel mount (female) molded connector on the other, providing a well-secured, easy to access DisplayPort connection on any machine port or faceplate.

Backed by StarTech.com's Lifetime Warranty

Certifications, Reports and Compatibility



Applications

- Extend your DisplayPort interface and allow you screw mount it to a panel

Features

- Latched connectors to reduce accidental disconnects

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Connector Plating	Nickel
	Fire Rating	CMG Rated (General Purpose)
	Number of Conductors	19
Connector(s)	Connector A	1 - DisplayPort (20 pin) Male
	Connector B	1 - DisplayPort (20 pin) Female
Environmental	Humidity	0 to 70%
	Operating Temperature	-5°C to 70°C
	Storage Temperature	10°C to 80°C
Physical Characteristics	Cable Length	0.9 m [3 ft]
	Cable OD	7.3 mm [0.3 in]
	Color	Black
	Product Length	0.9 m [3 ft]
	Weight of Product	94 g [3.3 oz]
	Wire Gauge	28 AWG
Packaging Information	Package Height	21 cm [8.3 in]
	Package Length	20 cm [7.9 in]
	Package Width	0.1 mm [0 in]
	Shipping (Package) Weight	94 g [3.3 oz]
What's in the Box	Included in Package	1 - 3ft. Panel Mount DisplayPort Cable

Product appearance and specifications are subject to change without notice.