

Product specification sheet

Revision dated 20 September 2019

1.	Product code	GS011*									
2.	Product description	Unicare Red Vinyl									
3.	Material	Vinyl									
4.	Inspection parameters	Criteria		Inspection level		AQL		Standard			
Dimensions		S-2		4.0		EN455-2					
Physical properties		S-2		4.0		EN455-2					
Water tight test (1,000ml)		G-1		4.0		EN455-1					
Visual defects		G-1		2.5		In-house					
5.	Glove dimensions	Dimensions		Size (mm)							
				XS	S	M	L	XL			
Product code		-	GS0112	GS0113	GS0114	GS0115					
Palm width		-	80 ± 10	95 ± 10	110 ± 10	≥ 110					
Length		-	≥ 240	≥ 240	≥ 240	≥ 240					
6.	Glove thickness	Point of thickness measurement				Nominal single wall (mm)					
Cuff (at beaded end)		0.05									
Palm (at centre of palm)		0.06									
Fingertip (at fingertip)		0.07									
7.	Physical properties	Parameters		Before aging			After aging				
Median force at break (N)		N/A			N/A						
Tensile strength (MPa)		Min 9			Min 9						
Ultimate elongation (%)		N/A			N/A						
8.	Proteins	None									
9.	Powder residue	Maximum 2.0 mg / glove									
10.	Cuff type	Beaded									
11.	Design	Ambidextrous									
12.	Surface	Smooth									
13.	Colour	Red									
14.	Quality assurance	Manufactured under ISO 9001 and ISO 13485									
15.	Weight (size medium)	4.5g									
16.	Standards compliant with	EN455-1	EN455-2	EN455-3	EN455-4	EN420	EN374-1	EN374-2	EN374-4	EN374-5	Food approved
						✓				✓	

The above data represents the product norm, which may be changed without notice and is intended as a guide only.