

CHERRY 



**USB CABLE 1.5
BRAIDED**

DATASHEET

CHERRY CABLE 1.5 BRAIDED

HIGH QUALITY USB-C TO USB-A CABLE

The USB CABLE 1.5 enables the connection between devices with a USB-C port and a PC or notebook with a USB Type-A port. The USB cable is not only ideal for compatible CHERRY products, but also for smartphones, tablets, headsets and other devices with a USB-C connection.

The USB CABLE 1.5 enables the connection between devices with a USB-C port and a PC or notebook with a USB Type-A port. The USB cable is not only ideal for compatible CHERRY products, but also for smartphones, tablets, headsets and other devices with a USB-C connection.



HIGHLIGHTS

- Connection cable USB-A to USB-C
- Suitable for data transfer (up to 480 Mbit/s possible) and charging process (max. 2,5 W)

SCOPE OF DELIVERY

- USB-A to USB-C Cable

TECHNICAL DATA

TEMPERATURE

Min. operating temperature	-20 °C
----------------------------	--------

Max. operating temperature	80 °C
----------------------------	-------

PRODUCT INFORMATION

Warranty	2 years warranty
----------	------------------

Product approvals	- CE
	- UKCA

PRODUCT VARIANTS

PART NUMBER

COLOUR

JA-0600-2

black/red

JA-0600-0

white

USB-A/-C CABLE [JA-0600-2]



Product colour: Black

Part number	JA-0600-2
EAN	4025112099779
UPC	840183606145

TEMPERATURE

Min. operating temperature	-20 °C
Max. operating temperature	80 °C

PRODUCT INFORMATION

Warranty	2 years warranty
Product approvals	- CE - UKCA
Dimensions inc. packaging	405 mm × 150 mm × 45 mm 34 g

USB-A/-C CABLE [JA-0600-0]



Product colour: White

Part number	JA-0600-0
EAN	4025112099762
UPC	840183606138

TEMPERATURE

Min. operating temperature	-20 °C
Max. operating temperature	80 °C

PRODUCT INFORMATION

Warranty	2 years warranty
Product approvals	- CE - UKCA
Dimensions inc. packaging	405 mm × 150 mm × 45 mm 34 g

© Cherry Europe GmbH

Cherrystraße 2 · 91275 Auerbach/OPf. · Germany
cherry-world.com · cherry.de

Sales Support · Technischer Support · eHealth Support

+49 9643 - 2061 - 100
www.cherry.de/de-de/kontakt

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.