

# Eaton 12BFGHD71

Catalog Number: 12BFGHD71

Eaton Bussmann series medium voltage BS air fuse, 71 A, 12 kV, 40 kA, 76 x 461 mm, With Striker

General specifications



Product Name	Catalog Number
Eaton Bussmann series medium voltage BS air fuse	12BFGHD71
	EAN
	5027590431927
Product Length/Depth	Product Height
461 mm	76 mm
Product Width	Product Weight
76 mm	4200 g
Compliances	Certifications
BS 2692-1	KEMA Certified

## Product specifications

## Resources

### Used with

A3354730 Fuse clip

### Type

Fuse

### Application

protection of primary side  
transformers  
used in fuse switch  
combination units, fuse  
bases and fuse switches

### Amperage Rating

71 A

### Fuse indicator

With Striker

### Fuse size

76 x 461 mm

### Breaking capacity

40 kA

### Installation technique

Air

### Performance Cat According To IEC 60282-1

Back-up

### Product application

Primary side transformer protection

### Rated frequency - max

50 Hz

### Rated frequency - min

50 Hz

### Release characteristic

Other

### Standard

British Standard

### Utilization category

Other

### Voltage type

AC

With striker

Yes

Class

Class back-up

Fuse shape

Cylindrical, offset bolted tags

Pre arc (I<sup>2</sup>T)

4.6 x 103

Resistance

10.6 ohms

Fuse diameter

76 mm

Interrupt rating

40 kAIC

Construction size

76 x 461 mm

Mounting method

Clip-in

Voltage rating

12 kV

Fuse type

BFGH



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia