

MLFB-Ordering data

6SL3202-0AE18-8CA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data

Rated current	9.00 A
Power loss	0.080 kW

Mechanical data

Width	207.0 mm (8.15 in)
Height	180.0 mm (7.09 in)
Depth	72.5 mm (2.85 in)
Degree of protection	IP20 / UL open type
Net weight	3.90 kg (8.60 lb)

Connections

Power connection motor

Version	screw terminals
Conductor cross-section	4.00 mm ²

PE connection

Version	M4 screw studs
---------	----------------