## Dynamic Series | Dynamic 3000 Series

TE Internal #: 2-2271457-4

TE Internal Description: D3950 HDR 4POS 1ROW Y KEY

View on TE.com >



#### Connectors > Terminal Blocks & Strips > PCB Terminal Blocks











Connector Style: Header

Connector System: Wire-to-Board

Number of Positions: 4

Centerline (Pitch): 7.5 mm [ .295 in ]

Number of Rows: 1

### **Features**

## **Product Type Features**

Block Type	PCB Mount
Header Type	Shrouded
Connector Style	Header
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Configuration Features	
Number of Positions	4
Number of Rows	1
Electrical Characteristics	
Voltage	300 VAC
Body Features	
Interlock	With

Black

Color



Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	.38 μm
Contact Mount	Through Hole
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	14.5 A
Mechanical Attachment	

Mounting Angle	Right Angle
Screwless Terminal Block	Yes
Connector Mounting Type	Board Mount

## **Housing Features**

Housing Color	Black
Housing Material	Thermoplastic
Centerline (Pitch)	7.5 mm[.295 in]

## **Usage Conditions**

Operating Temperature Range -30 – 105	5 °C[-22 – 221 °F]
---------------------------------------	--------------------

## Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

## Packaging Features

Packaging Method	Tray	
	,	

# **Product Compliance**

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2019 (201) Candidate List Declared Against: JUN 2018 (191) Does not contain REACH SVHC
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2019 (201) Candidate List Declared Against: JUN 2018 (191)
Halogen Content	Not Low Halogen - contains Br or Cl > 900



ppm.

## Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

# Compatible Parts



# Also in the Series | Dynamic 3000 Series



**Backplane Connector** Housings(2)



Connector Contacts(103)



PCB Terminal Blocks(12)



Rectangular Backshells & Clamps(2)





Rectangular Connector Hardware(7)



Rectangular Connector Housings(132)



Rectangular Connector Keying Plugs(1)



Standard Rectangular Connectors(291)



Terminal Block & Strip Mounting & Retention Accessories(1)



Wire-to-Board Connector Housings(2)



Wire-to-Board Headers & Receptacles(14)

# Customers Also Bought



TE Model / Part # T2070001033-000 CAM-33



TE Model / Part # T2070002033-000 CAF-33



TE Model / Part #5650992-5 TE Model / Part #1-ASSY, RECPT, ENH. TYPE C, EUROCARD,L-FREE,5



2271457-4 D3950 HDR 4POS 1ROW X KEY



TE Model / Part #1-2331743-4 D3950 REC 4POS 1ROW X KEY MARKED



TE Model / Part #2-2331743-1 D3950 REC 4POS 1ROW Y KEY



TE Model / Part #2232261-1 1394\_A RECEPTACLE UP RIGHT RA THRU HOLE



TE Model / Part # T1240160132-000 H16B-TGH-M32



TE Model / Part # T2050482101-000 HEEE-048-M



TE Model / Part # T2050482201-000 HEEE-048-F

### **Documents**



## **Product Drawings**

D3950 HDR 4POS 1ROW Y KEY

English

**CAD Files** 

3D PDF

3D

**Customer View Model** 

ENG\_CVM\_CVM\_2-2271457-4\_B.2d\_dxf.zip

English

**Customer View Model** 

ENG\_CVM\_CVM\_2-2271457-4\_B.3d\_igs.zip

English

**Customer View Model** 

ENG\_CVM\_CVM\_2-2271457-4\_B.3d\_stp.zip

English

## Datasheets & Catalog Pages

**DYNAMIC SPRING CLAMP SERIES** 

English

## **Product Specifications**

**Product Specification** 

English

## Agency Approvals

**UL Report** 

English