



Multi Purpose



Light Duty

Durable, touchscreen-compatible gloves that guard against electrostatic discharge

- **Specialized protection:** These HyFlex® gloves keep products safe, with EN 16350:2014 certification for protection from electrostatic discharge
- **Advanced tactility:** HyFlex® 11-819 ESD industrial gloves also possess superior tactile sensitivity and touchscreen compatibility
- **Improved durability and grip:** Their nitrile coating, with FORTIX™ Abrasion Resistance Technology, ensures ANSI/ISEA and EN compliant abrasion resistance and 2x more grip
- **Elevated comfort:** ZONZ™ Comfort Fit knitwork reduces strain in stress-prone areas
- **Varied capabilities:** They can also be used as part of a grounding chain in explosion hazard zones (ATEX)
- **Certified harm-free and skin-friendly:** HyFlex® 11-819 ESD work gloves also benefit from Oeko-Tex® and Dermatest® certification



Industries

- Aerospace
- Automotive
- Machinery and Equipment
- Logistics
- Industrial
- White Goods

Applications

- General handling
- Mounting and dismantling
- Machine tool operation
- Quality inspection
- Applications requiring dexterity and precision
- Compatible with consumer and industrial touchscreens
- Environments requiring ESD protection
- Warehouse and logistics operations

Key Features

- **ESD functionality:** Protecting products from electrostatic discharge
- **Ultra-thin nitrile foam coating:** Touchscreen-compatible tactility
- **FORTIX™ Abrasion Resistance:** 2x more grip, up to 20% more durability

Technologies



DMF free



FORTIX™

Abrasion Resistance Technology



Touchscreen Compatible



ZONZ™

Comfort Fit Technology

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4121A

EN 16350



STANDARD 100

1408033 Centexbel

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-819 ESD	Finishing: Palm dipped Coating Material: Fortix™ Foam Nitrile Liner Material: Nylon, Spandex, Carbon Cuff Style: Knitwrist	18	6, 7, 8, 9, 10, 11, 12	195-255 mm	Blue	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.