

## FEATURES

- **Polyacrylic material:** Offers excellent chemical resistance and durability
- **Maximum operating pressure of 2000 kPa:** Suitable for high-pressure applications
- **Maximum operating temperature of 200 °C:** Performs well in high-temperature environments
- **Rotary speed of 10 m/s:** Ensures effective sealing in dynamic applications
- **16 mm section:** Provides robust sealing capability
- **8 m length:** Offers ample material for multiple applications

## RS PRO 16mm Polyacrylic Gland Packing, 8m

RS Stock No: 606-577



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO gland packing is designed for sealing applications in various industrial settings. Made from durable polyacrylic material, it provides reliable performance in high-pressure and high-temperature environments. Ideal for use in pumps and valves, it ensures minimal leakage and enhanced operational efficiency.

## General Specifications

Maximum Operating Pressure	2000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	10 m/s
Section	16 mm
Sub Type	Gland Packing

## Mechanical Specifications

Length	8 m
Material	Polyacrylic

## Operation Environment Specifications

Maximum Operating Temperature	200 °C
-------------------------------	--------

## Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------