

TECHNIK ELECTRONIC SERVICE CASE

Service case with a comprehensive tool kit for data systems engineering

- 6400 **BERNSTEIN** **TECHNIK** with tool set
- 6415 **BERNSTEIN** **TECHNIK** without tool set
- 6400 Z **BERNSTEIN** **TECHNIK** with central safety code and tool set
- 6415 Z **BERNSTEIN** **TECHNIK** with central safety code without tool set

Description:

Case made from deep-drawn, impact-resistant, grained plastic, with a sturdy aluminium frame, dustproof and rainproof, acid- and scratch-resistant. Three removable plastic tray, 60 mm high, with adjustable partitions for measuring instruments, soldering iron and various accessories. The case has 2 locks.

Outside dimensions: 470 x 360 x 180 mm

Weight without tools: approx. 4.700 kg

Weight with tools: approx. 7.600 kg

Tool set:

No.	Description of individual tools	No.	Description of individual tools
1-909	Engineer's mirror , with handle, made entirely from BERNSTEINIT	14-654 VDE	Screwdriver , as above, blade 125 x 5.5 mm
2-126	Desoldering lever , slotted at one end, with plastic handle	14-691 VDE	Cross-recess screwdriver , Pozidriv, size 0, with VDE safety insulation, blade chrome vanadium, 60 mm long
2-127	Tin knife , with plastic handle, 115 mm	14-692 VDE	Cross-recess screwdriver , Pozidriv, as above, size 1, 80 mm long
2-128	Tin scraper , with plastic handle, 115 mm	5-006	Component tweezers , nickel-plated, with insulated jaws, for easy insertion and removal of plug-in transistors of various sizes
2-132	Spring hook , nickel-plated and insulated, 175 mm	5-049	Watchmaker's tweezers , 110 mm, stainless, sharply-pointed
2-145	Screwdriver with guide sleeve for slotted axles up to 3.2 mm Ø	5-107	Engineer's tweezers , made from steel, with bent tips, 150 mm, nickel-plated
2-161	Magnetic bar with double ball- and socket joint, slewable, 215 mm	5-115	Heat dissipating tweezers , 165 mm, nickel-plated, for use when soldering transistors, gold-bonded diodes etc.
2-265	2 Test prods , red and black, extremely slim, pointed and flexible, blade made from 1 mm steel wire	5-117	Engineer's tweezers , straight-flat-wide, 145 mm, nickel-plated
2-601	IC tweezers , nickel-plated, 125 mm, for gripping, inserting and removing IC's	5-161	Clamping scissors , 130 mm, stainless
3-127-2	"Slimline" side cutters , 115 mm, for soft wire only up to 1.0 mm, extremely slim head, box joint, compression spring, chrome-plated, with transparent insulation	5-181	Wire scraper , for wires 0.6 mm Ø, interchangeable cutters
3-131-1	Side cutters , 120 mm, chrome-plated, for hard wire up to 0.8 mm, for soft wire up to 1.5 mm, with BERNSTEINIT insulation	5-210	Needle files , 6-piece set
3-461-2	Round nose pliers , 130 mm, slim, box joint, compression spring, chrome-plated, with transparent insulation	5-301	Special scissors for cutting sheet-metal and wires, with serration, extremely slim, 110 mm, nickel-plated
3-462-2	Flat nose pliers , 130 mm, slim, box joint, compression spring, chrome-plated, with transparent insulation	5-501	Cable knife
3-481-2	Snipe nose pliers , 120 mm, angular, box joint, compression spring, chrome-plated, with transparent insulation	6-200	Socket spanner set , chrome vanadium, nickel-plated, 1 plastic handle, 7 socket spanners, 4.0, 5.5, 6.0, 7.0, 8.0, 9.0, 10.0 mm
3-565	Miniature water pump pliers , 130 mm, chrome-plated	6-750	Special open-end wrenches , 6-piece set, nickel-plated, material thickness 1.5 or 2 mm, 3 x 3.5, 4 x 4.5, 5 x 5.5, 6 x 6.5, 7 x 8, 9 x 10 mm
3-732-1	Combination pliers , 160 mm, chrome-plated, with BERNSTEINIT insulation	6-820	Set of allen hex sockets , 8 pieces, in plastic wallet, 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 5.5, 6.0, mm
3-761-10	Special assembly pliers for clamping rings, 1.5 mm – 2.8 mm, 140 mm, burnished, with adjusting screw	6-860	Electronic socket spanner set , in transparent box, 6 pieces, 3.0, 3.5, 4.0, 4.5, 5.0 mm
3-835-2	Wire strippers , 165 mm, narrow and slim, with adjusting screw and compression spring, chrome-plated, with transparent insulation	7-425	Dust brush
4-261	Cross-recess screwdriver , size 01, with plastic handle, blade made from chrome vanadium, nickel-plated, 25 mm long	7-428	Duster
4-301	Miniature screwdriver , with plastic handle, blade nickel-plated, 40 x 1.8 mm	7-435	Plastic-oiler , with screwcap made from brass
4-311	Screwdriver for headless screws , with plastic handle, blade made from chrome vanadium, nickel-plated, 80 x 2.8 mm	7-508	Steel tape measure , 30 cm, stainless
4-321	Chubby screwdriver , with plastik handle, blade made from chrome vanadium, nickel-plated, 25 x 4.0 mm	7-511	Digital caliper square , stainless, measuring range 150 mm, LCD-display mm/inches, depth-gauge, cross-points, in a wallet
4-343 VDE	Voltage tester , insulated blade, made from chrome vanadium, 60 x 3 mm	7-616	Pocket saw , in a wallet
4-351	Offset screwdriver , chrome vanadium, nickel-plated, 100 x 5 mm		
4-366	Cross-recess watchmaker's screwdriver , size 00		
4-391	Watchmaker's screwdriver , nickel-plated, with 4 interchangeable blades, 1.5, 2.0, 2.5, 3.0 mm		
4-407	Retaining screwdriver , 110 x 4 mm		
14-651 VDE	Screwdriver , with VDE safety insulation, blade made from chrome vanadium, 75 x 2.5 mm		
14-653 VDE	Screwdriver , as above, blade 100 x 4.0 mm		

To complete the set we recommend:

- 9-325 **Plastic box** with hinged lid and adjustable compartments, 200 x 130 x 30 mm
- 8-390 **Desoldering pump**, length 195 mm, 20 mm Ø
- 8-135 **ERSA "Multitip" soldering iron**, 15 W, 220 V

TECHNIK 6400 ELECTRONIC SERVICE CASE

A toolcase as a bordcase for the travelling engineer



The service case

- for the computer technology
- with special tool assortment
- for the professional



Service case **Technik 6400 Z**
with central safety code

