

# Axial kit EAMM-A-L38-40G-G2

Part number: 8197448

FESTO



 [General operating condition](#)

## Data sheet

| Feature                  | Value                 |
|--------------------------|-----------------------|
| Nominal length           | 32 mm                 |
| Mounting position        | optional              |
| Max. rotational speed    | 8000 rpm              |
| LABS (PWIS) conformity   | VDMA24364-B2-L        |
| Storage temperature      | -25 °C ... 60 °C      |
| Relative air humidity    | 0 - 95%               |
| Degree of protection     | IP40                  |
| Ambient temperature      | -10 °C ... 60 °C      |
| Mass moment of inertia   | 3.2 kgmm <sup>2</sup> |
| Transmittable torque     | 4.4 Nm                |
| Product weight           | 228 g                 |
| Interface code, actuator | L38                   |
| Interface code, motor in | 40G                   |
| Note on materials        | RoHS-compliant        |