

# M18 FTS210-O

## M18 FUEL™ ONE-KEY™ TABLE SAW

- The ONE-KEY™ M18 FUEL™ table saw delivers the power to rip cut at the same feed rate of an equivalent AC saw, with the ability to cut 190 m of 19 mm OSB board on one 12.0 Ah battery charge
- The HIGH OUTPUT™ system of tools elevates the M18 FUEL™ technologies to a new level and delivers extended performance and extended run time. These tools are designed to maximise the partnership with HIGH OUTPUT™ and FORGE™ batteries
- Rack and pinion sliding fence allows the fence to be adjusted accurately and easily from the front of the saw giving 622 mm of rip capacity
- 210 mm blade allows 63 mm depth of cut at 90 degrees
- ONE-KEY™ tool tracking & security offers a free of charge cloud-based tracking network and inventory management platform for your tools. ONE-KEY™ also features a remote locking functionality
- Quick change guard and riving knife allows the user to remove and adjust the riving knife and guard without the need to remove the throat plate
- Integrated carry handle allows easy transportation on and off the jobsite
- On board storage for all table saw attachments
- Vacuum adaptor supplied fits directly to all MILWAUKEE® dust extractors
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



### REDLITHIUM™



No load speed (rpm)	6,300
Blade diameter (mm)	210
Bevel capacity (°)	47
Rip capacity (mm)	622
Depth of cut capacity (mm)	63.5
Kit included	No batteries supplied, No charger supplied, No kitbox or bag supplied
Article Number	4933464722