

# Eaton 24AFIHA40

Catalog Number: 24AFIHA40

Air fuse-link, medium voltage, 40 A, AC 24 kV, BS AF4, 565 x 76.2 mm, back-up, BS, with striker

General specifications



Product Name	Catalog Number
Eaton Bussmann series medium voltage	24AFIHA40
BS air fuse	EAN
	5027590037723
Product Length/Depth	Product Height
565 mm	76.2 mm
Product Width	Product Weight
76.2 mm	6100 g
Certifications	
BS 2692-1	

## Product specifications

## Resources

### Used with

A3354730 Fuse clip

### Type

Fuse

### Application

protection of primary side  
transformers  
used in fuse switch  
combination units, fuse  
bases and fuse switches

### Amperage Rating

40 A

### Fuse indicator

With Striker

### Fuse size

76.2 x 565 mm

### Breaking capacity

16 kA

### Installation technique

Air

### Performance Cat According To IEC 60282-1

Back-up

### Product application

Primary side transformer protection

### Rated frequency - max

50 Hz

### Rated frequency - min

50 Hz

### Release characteristic

Other

### Standard

British Standard

### Utilization category

Other

### Voltage type

AC

With striker

Yes

Class

Class back-up

Fuse shape

Cylindrical

Pre arc (I<sup>2</sup>T)

1.2 x 103

Resistance

46.5 ohms

Fuse diameter

76 mm

Interrupt rating

16 kAIC

Construction size

76.2 x 565 mm

Mounting method

Clip-in

Voltage rating

24 kV

Fuse type

AFIH



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia