



ENGLISH

Datasheet

RS Pro Digital & Programmable HVAC Thermostat, 7 (Individual)/5 (Weekday)/1 days with LCD Display

RS Stock No: **823-4942**



Product Details

RS Pro digital and programmable HVAC thermostat comes with LCD display for effective measurements. This wireless thermostat is suitable for use with electric, gas or oil heating control system. This thermostat separates its functions into two units, the receiver plug socket and control centre. The receiver serves for wiring connections and heat on/off control and the control centre serves as user interface and temperature sensing control. This Thermostat features a large LCD display and optional programming period of either 7 individual day's or separate 5 days (weekdays) and 1 Day/1Day (Sat and Sun) programming with 4 or 6 separate time and temperature periods per day. You can keep the control centre nearby and control the temperature of the living area.

Features and Benefits

- Can be placed anywhere in the home to control the temperature of an area of the user's choice
- Not limited by power control wiring locations
- Link with the receiver via 433MHz RF, control distance 100M open site
- Large LCD display
- The screen displays the set temperature and the room temperature and time simultaneously
- Permanent user setting and program setting retention during power loss
- Optional temperature display of Celsius or Fahrenheit scale
- Both vacation mode and hold duration mode available for comfort and energy saving
- Optional programming period
- Display temperature recalibrates

**Specifications:**

Additional Features	LCD Display
Contact Rating	16 A
Contact Voltage	250 V ac
Maximum Temperature	+35°C
Minimum Temperature	+5°C
Program Duration	7 Days (Individual), 5 Days (Weekday), 1 Day
Supply Voltage	100 to 240 V ac
Temperature Range	+5 to +35°C