

216MVS6WH

Industrial Switched Interlocked Socket Outlet

2CMA163257R1000

Switched Interlocked Socket Outlet, vertical, Heavy Duty,
earthing sleeve position 6h, rated current 16A, IP67
watertight, 2-poles+earth



GENERAL

Product Name	Industrial Switched Interlocked Socket Outlet
Product ID	2CMA163257R1000
Function	Switched Interlocked Socket outlet, vertical, Heavy Duty
EAN	7392696632577
Catalog Description	Switched interlocked socket-outlet, vertical, Heavy Duty, 6h, 16A, IP67, 2P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2417133
E-Number Norway	2417133
E-Number Sweden	E2417133
Standards	IEC 60309-1, -2, -4
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	160 millimetre
Product Net Height	205 millimetre
Product Net Length	307 millimetre
Product Net Depth	307 millimetre
Product Net Weight	1.83 kilogram

TECHNICAL

Product Main Type	CMVS
Color	Blue
Number of Poles	3
Clock Position	6Hour
Rated Current	16 ampere
Rated Voltage	200 ... 250 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67 IP69
Cable Cross-Section	1.5...4 mm ²
Housing Material	Thermoplastic (PBT)
Plug Angle	
Product Group	Critical&Safe

PACKAGING

Package Width	215 millimetre
Package Height	165 millimetre
Package Gross Weight	1.83 kilogram
Package Length	335 millimetre
Package Units	box 1 piece