



ENGLISH

Product Datasheet

Mica Panel Radiator 1000W, UK Plug Version

RS 827-2884



Features:

Supplied with overheat safety protection and a thermal cut-off safety device for safety. The wide wheelbase between the castors on this electric flat-panel heater makes it easier to move around the room without tipping or falling

This heater provides a radiative heat output which warms people and objects in front of it, rather than heating and drying out the air, making a room more comfortable.



RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.



ENGLISH

Energy-efficient heat output

Three power output settings

Adjustable thermostat

Overheat safety cut-out

Wall mountable or floor stand

Power indicator light

Power 1000W

With 360° anti-tilt construction

With castors

Fitted with a Type G BS1363 UK plug

Dimensions: 600 x 275 x 560mm

Rated Voltage	Rated Frequency	Rated Power
220-240V	50Hz	1000W