

LGYT1N14

Neutral terminal block, Linergy, screw and screwless terminals, 14 holes, 3x25 mm² + 11x4 mm², with jumper

Main

Range	Linergy
Product or component type	Terminal block
Accessory / separate part category	Connection accessory
Range compatibility	Resi9 enclosure Pragma enclosure Kaedra enclosure enclosure
Colour	Blue

Complementary

Provided equipment	1.0 x jumper
Enclosure mounting	Flush Surface
[In] rated current	63 A
[Ue] rated operational voltage	440 V AC
Number of terminal blocks	1 neutral (screw and screwless terminals) with 14 outgoers
Distribution block outgoers	3 x 25 mm ² for neutral 11 x 4 mm ² for neutral
Connections - terminals	Screwless terminals (neutral) , 11.0 x 6 mm ² (rigid) Screw terminals (neutral) , 3.0 x 25 mm ² (semi-rigid) Screwless terminals (neutral) , 11.0 x 4 mm ² (flexible) Screw terminals (neutral) , 3.0 x 25 mm ² (flexible) Screwless terminals (neutral) , 11.0 x 6 mm ² (semi-rigid) Screwless terminals (neutral) , 11.0 x 4 mm ² (flexible with ferrule) Screw terminals (neutral) , 3.0 x 16 mm ² (rigid)
Free slots	2 for jumper to connect an other terminal block
Width	67.2 mm
Height	45.5 mm
Depth	40.5 mm
Market segment	Small commercial Residential

Environment

Ambient air temperature for storage	-25...60 °C
-------------------------------------	-------------

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins