

Features

- Flush cutter with foil safety clip for the cutting of copper wire and other soft materials.
- Steel thickness 3 mm.
- For copper wire Ø 1.30 mm (16 awg)
- The safety clip allows to cut wires to stand still on the tip of the tool, avoiding the "uncontrollable flight" of the cut parts.
- Tool is equipped with a return spring designed to have a constant force, thus reducing operator effort.
- Ergonomic anti-slip bicomponent handle for a safe, light and comfortable grip.
- Anti-reflection phosphating surface treatment.
- Laser marking.
- Made in Italy.

RS PRO Flush cutting edge. Medium head.

RS Stock No.: (0429718)



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- Made in Italy with high carbon steel and undergo a controlled atmosphere heat treatment.
- Flush cutter for copper wire max $\varnothing$ 1.30 mm (16 awg).
- Safety clip allows to cut wires to stand still on the tip of the tool, avoiding the "uncontrollable flight" of the cut parts.
- The anti-reflection phosphating surface treatment ensures an accurate view of the work being carried out.
- The tools are joined with grounded holes and surfaces, thereby allowing precise movements.
- The anti-slip bi-material dolphin handle is created following ergonomic principles, thus guaranteeing a safe, light and comfortable grip for the operator even when used constantly for many hours.

General Specifications

Cutter Type	Flush cutter. Medium head.
With safety clip	YES
Material	High carbon steel
ESD Safe	NO

Mechanical Specifications

Cutting capacities	$\varnothing$ 1.30mm (16 awg) copper wire
Cutting force	5 kg
Steel thickness	2.5 mm
Blade angle	27°
Overall Length	138 mm
Weight	75 g

