

Eaton 248268

Catalog Number: 248268

Eaton Distribution parts. Penetration for neutral conductor with test connector, 63A, 50/60Hz, 1HP

General specifications



Product Name	Catalog Number
Eaton Distribution parts	248268
EAN	Product Length/Depth
4015082482688	80 mm
Product Height	Product Width
65.5 mm	17.5 mm
Product Weight	Compliances
0.116 kg	RoHS conform

Product specifications

Color

Gray

Insulation body material

Other

Connectable conductor cross section (fine strand) - max

25 mm²

Connectable conductor cross section (fine strand) - min

1 mm²

Connectable conductor cross section (fine-strand) with cable end sleeve - max

25 mm²

Connectable conductor cross section (fine-strand) with cable end sleeve - min

1 mm²

Connectable conductor cross section (multi-wired) - max

25 mm²

Connectable conductor cross section (multi-wired) - min

1 mm²

Connectable conductor cross section (solid-core) - max

25 mm²

Connectable conductor cross section (solid-core) - min

1 mm²

Mounting height - min

80 mm

Nominal current

63 A

Number of clamp positions per level

1

Number of levels

1

Operating temperature - max

40 °C

Operating temperature - min

-25 °C

Rated operational voltage (Ue) - max

230 V

Resources

Drawings

[eaton-dimensions-mas-zd7-p63.jpg](#)

Wiring diagrams

[Zd7_P63](#)

Width/grid dimension

175 mm

Suitable for conductor material

Copper

Mounting method

DIN rail (top hat rail) 35 mm

Connection position

Above

Electrical connection 1 type

Screw connection

Electrical connection 2 type

Other

Inflammability class of insulation material (UL 94)

Other



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia