

Product data sheet

Characteristics

NSYRCDR18

Spacial SF/SM 180° pneumatic door stop for 19" swing rack - 180°



Main

Range	Spacial
Accessory / separate part category	Enclosure accessory
Product or component type	Mechanical retainer
Application	Electronic application Multi-purpose
For enclosure nominal dimensions	D: 600 mm D: 800 mm D: 1000 mm
Mounting support	19" swing rack supports
Range compatibility	Spacial SF Spacial SM
Device composition	Fixing elements 1 pneumatic retainer
Quantity per set	Set of 1

Complementary

Fixing mode	By fixing element: 19" swing rack support By fixing element: structure of enclosure
Operating angle	180 °
Height	108 mm
Width	80 mm
Depth	570 mm

Packing Units

Package 1 Weight	510 g
------------------	-------

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.