

8008N

stub and stub turnbuckles self-coloured

CE

TECHNICAL DATA

- safety coefficient: 4

LABORATORY TESTS

- chemical analysis
- tensile test

AVAILABLE CERTIFICATES

- Technical product specifications
- Test report UNI EN10204 type 2.2
- CE Declaration of Conformity



	art.	Ø mm	≈ "	WFL kg	L min mm
080080205	8008N M5	M5	3/16	115	160
080080206	8008N M6	M6	1/4	160	180
080080208	8008N M8	M8	5/16	300	210
080080210	8008N M10	M10	3/8	470	250
080080212	8008N M12	M12	1/2	690	280
080080214	8008N M14	M14	9/16	940	340
080080216	8008N M16	M16	5/8	1290	380
080080218	8008N M18	M18	11/16	1660	410
080080220	8008N M20	M20	3/4	2130	440
080080222	8008N M22	M22	7/8	2630	480
080080224	8008N M24	M24	1"	3060	520
080080227	8008N M27	M27	1 1/8"	4000	560
080080230	8008N M30	M30	1 3/16"	4860	560
080080233	8008N M33	M33	1 1/4"	6040	600
080080236	8008N M36	M36	1 3/8"	6500	600
080080239	8008N M39	M39	1 1/2"	7900	600