



ENGLISH

Datasheet

RS Pro 213 Piece Tool Kit

RS Stock No: 125-3047

RS Pro Tool Cabinet and Tool Module Kit

Our great value 6 Draw Tool Cabinet is packed with a 213 piece Tool Kit fitted in EVA modules for excellent protection and tool organisation. The selected tools were chosen with engineers in mind to make sure that you have a comprehensive range at hand. Ready to use and an excellent choice for industrial and automotive applications.



6 Drawer Tool Cabinet

Our professional Tool Cabinet is made from premium quality steel and features a scratchproof electrostatic powder coated finish.

Each Drawer can accommodate up to 3 EVA Tool Modules and can be fully extended to offer greater access. Also the drawers feature the Smart-Lock system which prevents accidental opening when the cabinet is moved. The heavy-duty wheels made from oil resistant rubber, with two fixed and two swivel.

Features and Benefits

- Recessed worktop with a high-quality mat to ensure a convenient working area
- Holders for spray cans and paper rolls
- Low friction telescopic ball bearing slides ensuring smooth operation
- Fitted with an emergency brake

RS 39 Piece Screwdriver and Bit Set Tool Module



- 3 x 75 mm Slotted Screwdriver
- 4 x 100 mm Slotted Screwdriver
- 5.5 x 125 mm Slotted Screwdriver
- 6.5 x 150 mm Slotted Screwdriver
- PZ1 x 80 mm Pozidriv Screwdriver
- PZ2 x 100 mm Pozidriv Screwdriver
- VDE Insulated Voltage Tester
- 4, 5.5, 6.5 mm Slotted Bits
- PH1 (x2), PH2 (x3), PH3 Phillips Bits
- PZ1 (x2), PZ2 (x3), PZ3 Pozidriv Bits
- T10, T15, T20 (x2), T25, T27, T30 (x2), T40 Torx Bits
- 2, 2.5, 3, 4, 5, 6 mm Hexagon Bits
- 1/4in x 60 mm Power Tool Bit Holder

RS 15 Piece T-Handle & Ball Point Hex Key Tool Module



- 2, 2.5, 3, 4, 5, 6 mm T-Handle Hex key
- 1.5, 2, 2.5, 3, 4, 5, 6, 8, 10 mm Ball End Hex Key

RS 3 Piece Soft Grip Pliers Tool Module



- 180 mm Combination Pliers
- 160 mm Diagonal Cutters
- 160 mm Long Nose Pliers

RS 3 Piece pliers and Wrench Tool Module



- 50 mm Water-pump Pliers
- 240 mm Grip pliers
- 250 mm Adjustable Wrench

RS 10 Piece Precision Pliers and Screwdriver Tool Module



- 110 mm Oval Head Electronics Cutter
- 120 mm Short Needle Nose Electronics Pliers
- 140 mm Long Needle Nose Electronics Pliers
- 115 mm Stainless Steel Tweezers
- 1.5 x 60 mm Electronics Slotted Screwdriver
- 2.0 x 60 mm Electronics Slotted Screwdriver
- 2.5 x 80 mm Electronics Slotted Screwdriver
- 3.0 x 80 mm Electronics Slotted Screwdriver
- PH00 x 60 mm Electronics Phillips Screwdriver
- PH0 x 60 mm Electronics Phillips Screwdriver

RS 23 Piece 1/2 in Socket Set Tool Module



- Steel construction for excellent strength and durability
- Soft comfortable reversible quick release ratchet handle for reduced fatigue and easy speedy bit replacement
- Supplied with a full accessory assortment for a complete kit
- Bright red foam helps identify missing parts quickly

RS 52 Piece 1/4 in Socket and Hex Key Set Tool Module



- Complete 6 point socket, bit and bit socket set
- Steel construction for excellent strength and durability
- Soft comfortable reversible quick release ratchet handle for reduced fatigue and easy speedy bit replacement
- Long arm L shaped key set supplied in a plastic caddy with size markings for easy pocket storage and quick identification of missing tools
- Supplied with a full accessory assortment for a complete kit
- Bright red foam helps identify missing parts quickly

RS Pro 16 Pieces Combination Spanner Tool Module



- Combination Spanner 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 21, 22 mm

RS 6 Piece Measuring and Cutting Tool Module



- 145 mm Electricians Shears/ Scissors
- 250 mm Straight Snip
- 18 mm Snap Off Utility Knife
- 5 m x 19 mm Tape Measure
- 300 mm Stainless Steel Rule
- 20 Leaf Metric Feeler Gauge

RS 11 Piece Engineer and Needle File Tool Module



- 200 mm Bastard Cut Hand, Half Round, Round, Square, Three Square Engineer File
- 160 mm Needle Flat, Hand, Half Round, Round, Square, Three Square File Needle File

RS 7 Piece VDE Insulated Screwdriver Tool Module



- 3 x 100, 4 x 100, 5.5 x 125, 6.5 x 150 mm VDE Insulated Slotted Screwdrivers
- PH x 80, PH2 x 100 mm VDE Insulated Phillips screwdrivers
- VDE Voltage Tester

RS 29 Piece 1/2 in Torx, Hex and XZN Bit Socket Tool Module



- 8 x Short Torx Socket Bits, T20 to T60
- 4 x Long Torx Socket Bits T30 to T50
- 7 x Short Hex Socket Bits 5 to 14 mm
- 4 x Long Hex Socket Bits, 6 to 12 mm
- 5 x Short XZn Socket Bits, M05 to M12
- 1 x Short L Hex Key, 2.5 mm