

Features

- Excellent molten splash and flame resistance
- Continuous working temperature of 200°C (500°F)
- Superb abrasion and moisture resistance
- Highly flexible
- Provides protection from ozone and UV
- Insulates against energy loss in piping and hosing
- Max short time exposure 1650°C (3000°F)

RS PRO Fire Sleeve Range



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO Fire Sleeves are designed to protect hoses, wires and cables from the hazards of high heat and occasional flame. Constructed from braided fiberglass yarns in a flexible substrate it is then coated with high grade silicone rubber. The thick formulation of silicone rubber sheds molten splash, slag, welding splatter, electrical or grinding sparks and contamination. RS PRO Fire Sleeve's key applications are protecting hydraulic hoses, cables and wiring. Used in metallurgy, steel mills, glass works, marine industry and petrochemical industry.

Approvals

Declarations	Compiles with EN 45545-2 Tested to ISO 11925-2
Standards Met	Meets requirement for IEC 60695-11-10 Classified as HB and V0 Meets requirements for UL94 V0,V1,V2

1m Fire Sleeves

RS PRO Stock Number	Length (m)	Internal Diameter (mm)
457-331	1	4
457-332	1	6
457-334	1	8
457-371	1	10
457-372	1	14
457-373	1	16
457-375	1	19
457-376	1	20
457-378	1	22
457-379	1	25
457-381	1	28
457-382	1	32
457-384	1	35
457-385	1	38
457-387	1	41
457-388	1	44
457-389	1	51
457-390	1	57
457-391	1	63
457-393	1	70
457-394	1	76
457-395	1	83
457-290	1	89
457-292	1	95
457-365	1	102

5m Fire Sleeves

RS PRO Stock Number	Length (m)	Internal Diameter (mm)
457-294	5	4
457-296	5	6
457-297	5	8
457-335	5	10
457-337	5	12
457-338	5	14
457-339	5	16
457-340	5	19
457-341	5	22
457-343	5	25
457-344	5	28
457-345	5	32
457-347	5	35
457-348	5	38
457-350	5	41
457-351	5	44
457-353	5	51
457-354	5	57
457-356	5	63
457-357	5	70
457-359	5	76
457-360	5	83
457-362	5	89
457-363	5	95
457-329	5	102

15m Fire Sleeves

RS PRO Stock Number	Length (m)	Internal Diameter (mm)
457-366	15	4
457-367	15	6
457-369	15	8
457-299	15	10
457-300	15	12
457-301	15	14
457-303	15	16
457-304	15	19
457-306	15	22
457-307	15	25
457-309	15	28
457-310	15	32
457-312	15	35
457-313	15	38
457-315	15	41
457-316	15	44
457-317	15	51
457-319	15	57
457-321	15	63
457-322	15	70
457-323	15	76
457-325	15	83
457-326	15	89
457-328	15	95
457-293	15	102