




Datasheet

Product Name:	UL1569 22AWG
Product Discription:	UL1569 22AWG
Specification No.:	SPEC-UL1569-22AWG
Customer's Name:	

Description					Construction						
Rated Voltage:		300V			Conductor		Stranded Tinned Copper				
Rated Temperature:		105℃			Size(AWG)		22				
Reference Standard:		UL758,UL1581			Construction(±0.004mm)		17/0.16				
Cross Section					Stranded Dia.(mm)Ref.		0.76				
					Insulation Material		PVC				
					Insulation Color		ANY COLOR				
					Ave Thickness(mm)		0.38				
					Min Thickness(mm)		0.33				
					Insulation Dia.(±0.08mm)		1.58				
Marking					Remark:						
E254881  AWM STYLE 1569 22AWG 105℃ 300V VW-1 C  AWM I A 105℃ 300V FT1 -LF- ELETECK					8840910 Brown		8840926 Grey				
					8840922 Orange		8840929 Yellow				
					8840935 Violet						
					Characteristics				Customer Approve		
Internal wiring of appliances or electronic equipment where not subjected to movement or mechanical damage.					Test Item			Standard Value			 <