

# SceneSwitch LED Lamps

LED Scene Switch 50W GU10 WW 36D ND 1BC/4



Some situations call for cool light, others benefit from the ambiance of a warm cozy glow. With Philips SceneSwitch LED lamps, you can have different light settings from just one bulb, candle or spot. And you don't need a dimmer! Optimize your lighting for relaxing, hobbies, recreation or working. Simply at the flick of a switch. And that's your existing switch! No extra installation is required.

**PHILIPS**

## Product data

### • General Information

Cap-Base	GU10
Nominal Lifetime (Nom)	15000 h
Switching Cycle	100000X
Technical Type Setting(s)	4.5/2.8/1.3-50 W

### • Light Technical

Color Code	827/825/822 [ CCT of 2700K/2500K/2200K]
Beam Angle (Nom)	36 °
Color Designation	Warm White (WW)
Rated Beam Angle	36 °
Correlated Color Temperature Setting(s)	2700/2500/2200 K
Luminous Efficacy (rated) (Nom)	77 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated) Setting(s)	350/140/40 lm

### • Operating and Electrical

Power (Rated) Setting(s)	4.5/2.8/1.3 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s

Power Factor (Nom)	0.45
Voltage (Nom)	220-240 V

### • Temperature

T-Case Maximum (Nom)	87 °C
----------------------	-------

### • Controls and Dimming

Dimmable	No
----------	----


### • Approval and Application

Energy Saving Product	Yes
Suitable For Accent Lighting	Yes
Energy Efficiency Label (EEL)	A+
Energy Consumption kWh/1000 h	5 kWh

### • Product Data

Full product code	871869659858000
Order product name	LED Scene Switch 50W GU10 WW 36D ND 1BC/4
EAN/UPC - Product	8718696598580
Order code	929001264301
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	929001264301
Net Weight (Piece)	0.052 kg

## Dimensional drawing




### GU10 230V 6-50W 355lm 36D 2700K E27 ND

Product	D	C
LED Scene Switch 50W GU10 WW 36D ND 1BC/4	50 mm	55 mm

Accent Lighting - Spots


**GU10 4.5W2700K 35D 9290012643**

374lm (90° cone 345lm)



2016-06-13

## SceneSwitch LED Lamps



© 2016 Philips Lighting Holding B.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2016, September 14  
data subject to change