

Eaton 160MJ29-6

Catalog Number: 160MJ29-6

Eaton Bussmann series low voltage british standard fuse, 160A, AC 415 V, V88/J, 38 x 101 mm, gU



General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage british standard fuse	160MJ29-6
	EAN
	5027590437073
Product Length/Depth	Product Height
110 mm	42 mm
Product Width	Product Weight
195 mm	185.6 g
Compliances	Certifications
CE Marked	BS
RoHS Compliant	IEC 60269
	EAC

Electrical data

Amperage Rating

160 A

Voltage rating

415 V

Voltage type

AC

Breaking capacity

80 kA

Product specifications

Application

feeder pillars

Fuse type

MJ29

Fitted with:

Slotted tags

Connection

Bolt-on

Resources

Catalogs

[CA134002EN](#)

Declarations of conformity

[CE Feeder pillar fuse-links](#)

[UKCA Feeder pillar fuse-links](#)

Multimedia

[Eaton Bussmann - Red Spot fuse links](#)

Technical service bulletins

[Datasheet - 160MJ29-6](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
[Eaton.com](#)

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)