



NOTES:

1. INSERTION LOSS: 0.75 dB MAX.
2. OPERATION TEMP: -20°C TO +70°C.
3. PRODUCT COMES WITH DUST CAPS. (NOT SHOWN)
4. MATERIALS:
 SLEEVE:
 SINGLE-MODE - CERAMIC (ZIRCONIA)
 MULTI-MODE - PHOSPHORUS BRONZE
 HOUSING - DELRIN, BLACK
 ADAPTER - THERMOPLASTIC
 ADAPTER MOUNTING CLIPS - STAINLESS STEEL
5. FOR MOUNTING SCREWS TO BE SHIPPED WITH ASSEMBLY AND INDIVIDUAL PACKAGING, ADD SUFFIX -PKG TO PART NUMBER.
6. WHEN MOUNTING ASSEMBLY, USE A SCREW TORQUE OF 10 INCH-POUNDS MAXIMUM.
7. THIS PRODUCT IS RoHS COMPLIANT.

**RECOMMENDED
PANEL CUT-OUT**

PART NUMBER	SC2 ADAPTER	ADAPTER COLOR
EHSC2	SINGLE-MODE	BLUE
EHSC2M	MULTI-MODE	BEIGE

CUSTOMER DRAWING

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
					SIZE	WIDTH	MULT	LBS/M	TEMPER
					FINISH			MATERIAL	
					SPEC No.			SPEC No.	
					FIRST USED ON		SCALE 1:1		
A	26348	2/27/29	RS	TJK	DATE DRAWN	BY	CHKD	APVD	Switchcraft®
REV	ECO NUMBER	DATE	BY	APVD	5/12/08	JGK	RS	TJK	
REVISIONS					DO NOT SCALE DRAWING				
					NAME			PART No.	
					E SERIES SC/SC FIBER OPTIC ADAPTER, RoHS			EHSC2 SERIES	
					REV A				

