


Rhino™ 5200



Portable Labeling Tool that Saves You Time and Money

- Meets all ANSI, TIA/EIA-606-B labeling standards
- Exclusive, one-touch “Hot Keys” automatically size, space and format label text for electrical and patch panels, terminal and 110 blocks, wire and cable flags, horizontal and vertical wraps, vertical and fixed-length applications
- Prints Code 39 and Code 128 bar codes on 19 mm wide labels
- Labels up to 77% faster than the competition*
- Last-label memory; storage for up to 100 of the labels you use most
- Symbol library includes more than 100 pre-programmed industry symbols
- Integrated rubber bumpers for slip-resistant grip, protection against damage from falls



*Based on independent testing of Rhino 5200 vs. Panduit LS8, Brady BMP21, Brother PT1650 measured in number of key strokes when making patch panel labels and all associated wire and faceplate labels

Single Unit Includes:

- Rhino 5200 Label Printer
- 19 mm White Vinyl Label Cartridge
- User Manual CD-ROM
- Quick Reference Guide



Kit Includes everything in single unit, plus:

- 9 mm White Vinyl Label Cartridge
- AC Adapter
- Carry Case
- Rechargeable Lithium-ion Battery



Quick Specs

Unit Dimensions (H x W x L)	234 x 124 x 64 mm
Weight (excluding battery)	0.8 Kg
Mac®/PC Compatible	No
Accepts Label Sizes	6mm, 9mm, 12mm, 19mm
Tape Platform	IND Rhino™
Resolution	180 dpi
Printing System	Thermal Transfer
Print Speed	10mm/sec
Barcodes	Yes, Code 39 & Code 128
Cutter Type	Manual
Batteries	6 AA or Rechargeable (not included)
AC Adapter	Yes (included in kit only)
Country of Origin	China

Item Number	Description		Length (cm)	Width (cm)	Height (cm)	Weight (kg)	QTY	EAN	Customer Price	
S0841460	RHINO 5200 ABC ENG/NL/FR/DE	Unit	8.8	15.6	28.5	1.0	1	3501170841464		
		Shelf	-	-	-	-	-	-	-	
		Case	27.5	19.4	34.5	4.4	4	13501170841461		
		Pallet	120.0	80.0	118.5	236.7	192	-		
S0841390	RHINO 5200 ABC KIT UK	Unit	12.0	37.5	33.0	2.4	1	3501170841396		
		Shelf	-	-	-	-	-	-	-	
		Case	38.6	37.2	34.7	7.5	3	13501170841393		
		Pallet	120.0	80.0	119.1	160.9	54	-		
Accessories										
S0902390	RHINO 5200 Case	Unit	12.0	37.5	33.0	1.4	1	3501170902394		
S0721430	RHINO AC Adapter	Unit	11.5	5.9	8.9	0.2	1	5411313400756		
S0895840	Rechargeable battery	Unit	8.5	3.2	8.9	0.1	1	3501170895849		



IND Vinyl

Ideal for both indoor and outdoor applications. Available in the widest range of colors that meet OSHA, ANSI and ISO color standards.

- UL recognized component to UL 969
- RoHS compliant
- Temperature rating: -40°C to 80°C

IND Flexible Nylon

Specifically designed for curved surfaces and wire and cable marking.

- UL recognized component to UL 969
- RoHS compliant
- Temperature rating: -10°C to 80°C

IND Permanent Polyester

Professional, polished finish ideal for panels, blocks, faceplates, shelves, bins, beams and more.

- UL recognized component to UL 969
- RoHS compliant
- For flat surfaces only
- Temperature rating: -40°C to 150°C

IND Heat-Shrink Tube

For high-end cable identification. A 3:1 shrink ratio helps ensure a secure fit on wires and cables.

- Meets MIL-M-81531, MIL-STD-202G, SAE-DTL-23053/5 (Class 1 & 3)
- UL recognized as a component to UL 224
- RoHS compliant
- Temperature rating: -55°C to 135°C

IND Compatible Labels												
Width	Length	A	A	A	A	A	A	A	A	A	A	A
IND VINYL												
9mm	5.5m	18443	-	-	-	-	-	1805437	-	-	-	-
12mm	5.5m	18444	-	18432	18435	1805413	1805416	1805435	1805414	1805243	1805415	1805412
19mm	5.5m	18445	-	18433	18436	1805419	1805422	1805436	1805420	1805417	1805421	1805418
IND PERMANENT POLYESTER												
6mm	5.5m	1805442	1805440	-	-	1805441	-	-	-	-	-	-
9mm		18482	18508	-	-	18485	-	-	-	-	-	-
12mm		18483	622289	-	-	18486	-	-	-	-	-	-
19mm		18484	622290	-	-	18487	-	-	-	-	-	-
IND FLEXIBLE NYLON												
12mm	3.5m	18488	-	18490	-	-	-	-	-	-	-	-
19mm	3.5m	18489	-	18491	-	-	-	-	-	-	-	-
IND HEAT-SHRINK TUBE												
6mm	1.5m	18051	-	18052	-	-	-	-	-	-	-	-
9mm		18053	-	18054	-	-	-	-	-	-	-	-
12mm		18055	-	18056	-	-	-	-	-	-	-	-
19mm		18057	-	18058	-	-	-	-	-	-	-	-

Country of Origin: Belgium

DISTRIBUTED BY:
 Newell Europe Sàrl
 Chemin de Blandonnet 10
 1214 Vernier – Switzerland
 WWW.DYMO.COM

13-0103

INTERNAL USE ONLY. NOT FOR DISTRIBUTION.

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.



A *Newell Rubbermaid* Brand

©2014 Newell Europe LLC

A NewellRubbermaid Company™

SCHAWK!

RMZ Milenia Business Park
Campus - 2, 5th Floor
No. 143, Dr.M. G. R. Road
Kandanchavadi | Chennai 600 098 India
T +91 44 4213 7777 | www.schawk.com



Use the PANTONE MATCHING SYSTEM for accurate color reproduction

VERSION	JOB DESCRIPTION : NRM_EU_Writing_Dymo_1362812_EMEA Product Handbooks_UK Masters FILE NAME : DY_1362812_2014_EMEA_RH5200_TechSheet_v5.indd	BRAND : WRITING-DYMO
5 Date: 10-10-2014 Operator : HL	SCHAWK JOB # : 310253P NRM JOB # : 1362812 SAP / FG # : N/A COMPONENT # : N/A NO OF PAGES : 2	DIELINE : XXXXX UPC : XXXXX VENDOR : XXXXX

Note :