

Impact wrench XGT®

TW004G

40V max • 1/2" • 350 Nm • 0 – 3 200 min⁻¹

Extra-compact and efficient brushless impact wrench with four power settings

Powerful and extra-compact, 144 mm-long, 1/2" drive impact wrench. Small size and light weight make this tool easy to use, while offering a max. fastening torque of 350 Nm. Four power settings. 2 LEDs with pre-glow and afterglow functions.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Brushless Motor	✓
No load speed	0 - 1000 / 1800 / 2600 / 3200 min ⁻¹
Max Fastening Torque Impact Drill	100 / 160 / 210 / 350 Nm
Nut-busting torque	630 Nm
Tightening Capacity Standard Bolt	M10 - M20
Impacts per Minute (IPM)	0 - 1800 / 2600 / 3400 / 4000 min ⁻¹
Drive Square	1/2 "
Sound Power Level (L _{WA})	110 dB(A)
Sound Pressure Level (L _{pA})	102 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,8 - 3,1 kg

User benefits

- Electronic 4 stage impact power selection for added versatility
- 3 modes of reaction time for automatic stop available both in forward and reverse rotation modes
- Reverse rotation Auto Stop mode stops after the bolt/nut loosened enough
- Twin LED lights with pre-glow and afterglow functions for better illumination and more accurate work
- Ergonomic soft grip handle provides increased comfort
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Brushless maintenance-free and long-life motor
- Battery protection system automatically shuts off power when the battery level is low
- Style of socket retention: C-ring
- Constant speed control maintains fastening torque by minimising the rotation speed reduction caused by decreased battery capacity

Link to product - www.makitauk.com



Related products

■ Optional AC

412393-7

Battery Cover For Xgt® Batteries



821550-0

Makpac case (2)



835R29-3

Inner tray (2)



■ Other

User manual

Parts drawing