

Features

- Non-conductive
- Anti-magnetism
- Nylon lock body
- Nylon shackle

RS PRO Padlocks

RS Stock No.: 0217694



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Nylon lock body and nylon shackle combined perfectly, with better non-conductive, anti-magnetism quality.

Nylon shackle is non-conductive, especially suitable for military, mining and power areas.

Lock body dimensions: Length 45mm, Width 40mm, Thickness 19mm; Shackle Diameter 6mm, Shackle Height 38mm.

All fittings of padlock are anti-magnetism and insulation.

Includes 2 sets lock body warning labels, where you can write the owner's information.

General Specifications

| | |
|----------------------|-----------------|
| Lock Type | Key |
| Material | Nylon |
| Bluetooth | No |
| Keyed Alike | Keyed to differ |
| Indoor/Outdoor | Indoor |
| Weather Proof | No |
| Colour | Red |
| Quantity Per Package | 1 |
| Packaging Type | Box |
| Body Shape | Square |
| Shackle Shape | U |
| Shackle Material | Nylon |
| Key Retaining | Yes |

Mechanical Specifications

| | |
|----------------------------|------|
| Shackle Length | 38mm |
| Body Width | 40mm |
| Shackle Diameter | 6mm |
| Body Thickness | 19mm |
| Vertical Shackle Clearance | 38mm |

| | |
|------------------------------|-------|
| Horizontal Shackle Clearance | 20mm |
| Overall Width | 40mm |
| Body Height | 89mm |
| Weight | 74.5g |

Approvals

| | |
|---------------------------|----|
| Compliance/Certifications | CE |
|---------------------------|----|