

## Ferrule - A 16 -25 - 1090632

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Ferrule, length: 25 mm, color: silver

### Your advantages

- ✓ The dimensions of the ferrules conform to DIN 46228-1
- ✓ The ferrules without plastic sleeve are made from soft tin-plated electrolytic copper



### Key Commercial Data

Packing unit	250 pc
Minimum order quantity	250 pc
GTIN	 4 055626 900353
GTIN	4055626900353
Weight per Piece (excluding packing)	0.800 g
Custom tariff number	85369010
Country of origin	Germany
Sales Key	BH3412

### Technical data

#### Dimensions

Length (b)	25 mm
Maximum stripping length	25 mm
Inner dimension of the insulating collar (d)	7.5 mm
Ferrule diameter	5.8 mm
Sleeve wall thickness	0.2 mm

#### Ambient conditions

Short-term temperature	120 °C
Max. permanent temperature	105 °C

# Ferrule - A 16 -25 - 1090632

## Technical data

### General

Color	silver
Material	CU-DHP
Coating	tin-plated (galvanic)
Conductor category	Stranded conductors, class 2, 5, 6 / B, C, K, M

## Classifications

### eCl@ss

eCl@ss 10.0.1	27400201
eCl@ss 11.0	27400201
eCl@ss 9.0	27400201

### ETIM

ETIM 6.0	EC000005
ETIM 7.0	EC000005

## Approvals

### Approvals

#### Approvals

UL Listed / cUL Listed / CSA / CSAus / cULus Listed / cCSAus

#### Ex Approvals

### Approval details

UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	E488001
-----------	---	---	---------

cUL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	E488001
------------	---	---	---------


CSA		<a href="http://www.csagroup.org/services-industries/product-listing/">http://www.csagroup.org/services-industries/product-listing/</a>	247397
-----	---	---	--------

## Ferrule - A 16 -25 - 1090632

### Approvals

CSAus		<a href="http://www.csagroup.org/services-industries/product-listing/">http://www.csagroup.org/services-industries/product-listing/</a>	247397
-------	---	---	--------

cULus Listed			
--------------	---	--	--

cCSAus			
--------	---	--	--

### Accessories

#### Accessories

#### Crimping tool

Crimping pliers - CRIMPFOX 25R - 1212039



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 10 mm<sup>2</sup> ... 25 mm<sup>2</sup>, lateral entry, WM crimp