

## PP FO CAB-ASSY-18M-2xPP Metal LCD SM OV



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                     |
|--------------------|-------------------------------------------------------------------------------------|
| Part number        | 33 58 231 0180 026                                                                  |
| Specification      | PP FO CAB-ASSY-18M-2xPP Metal LCD SM OV                                             |
| HARTING eCatalogue | <a href="https://harting.com/33582310180026">https://harting.com/33582310180026</a> |

### Identification

|                          |                             |
|--------------------------|-----------------------------|
| Category                 | System cabling              |
| Series                   | HARTING PushPull (V4)       |
| Element                  | Cable assemblies            |
| Specification            | Pre-assembled on both sides |
| Connector 1              | HARTING PushPull (V4)       |
| Connector 2              | HARTING PushPull (V4)       |
| Type of cable            | FO cable                    |
| Description of the cable | Singlemode                  |

### Version

|                |            |
|----------------|------------|
| Cable length   | 18 m       |
| Core structure | 9 / 125 µm |

### Technical characteristics

|                                        |                |
|----------------------------------------|----------------|
| Limiting temperature                   | -40 ... +70 °C |
| Degree of protection acc. to IEC 60529 | IP65 / IP67    |
| Cable diameter                         | 6.5 mm         |

### Material properties

|                         |                    |
|-------------------------|--------------------|
| Material (hood/housing) | Metal              |
| Material (cable)        | PUR (polyurethane) |
| RoHS                    | compliant          |
| ELV status              | compliant          |



**Pushing Performance**  
 Since 1945

## Material properties

|                                      |               |
|--------------------------------------|---------------|
| China RoHS                           | e             |
| REACH Annex XVII substances          | Not contained |
| REACH ANNEX XIV substances           | Not contained |
| REACH SVHC substances                | Not contained |
| California Proposition 65 substances | Not contained |

## Specifications and approvals

|                |                                |
|----------------|--------------------------------|
| Specifications | IEC 61076-3-106 Variant 4 (V4) |
|----------------|--------------------------------|

## Commercial data

|                                |                                              |
|--------------------------------|----------------------------------------------|
| Packaging size                 | 1                                            |
| Net weight                     | 104 g                                        |
| Country of origin              | Czechia                                      |
| European customs tariff number | 85447000                                     |
| GTIN                           | 5713140153301                                |
| eCl@ss                         | 27060390 Ready-made data cable (unspecified) |
| ETIM                           | EC002599                                     |
| UNSPSC 24.0                    | 26121600                                     |