

MILWAUKEE TOOL

Milwaukee Electric Tool Corporation
BROOKFIELD, WI 53005
USA
Tel: +1 (262) 781-3600 • Fax: +1 (262) 790-6333

Milwaukee Asia Office
29/F, Tower 2, Kowloon Commerce Centre,
51 Kwai Cheong Road, Kwai Chung, Hong Kong
Tel: +852-2492-2181 • Fax: +852-2490-4778

Distributed by:

16/5/2022


All data incl. service and warranty conditions as well as product range are subject to change without notice.
Pictures not binding. No liability for printing errors or mistakes. © 2022 Milwaukee Electric Tool Corporation.
All trademarks are owned by Techtronic Cordless GP unless otherwise stated.

www.milwaukeetool.asia

Milwaukee™

M18 FUEL™

DRIVEN TO OUTPERFORM.™



POWERSTATE™ BRUSHLESS MOTOR

REDLINK PLUS™ INTELLIGENCE

REDLITHIUM BATTERY PACK

M18 FOPH
QUIK-LOK ATTACHMENT SYSTEM

FULL THROTTLE UNDER 1 SECOND

MORE POWER WITH POWERSTATE™ BRUSHLESS MOTOR

UP TO 1 KG LIGHTER

AVAILABLE ATTACHMENTS

PART OF THE QUIK-LOK™ ATTACHMENT SYSTEM

POWERHEAD WITH QUIK-LOK™



NEW



BRISTLE BRUSH ATTACHMENT
M18 FOPH - BBA

NEW



RUBBER BROOM ATTACHMENT
M18 FOPH - RBA

NEW



BRUSH CUTTER ATTACHMENT
M18 FOPH - BCA



STRING TRIMMER ATTACHMENT
M18 FOPH-LTA



HEDGE TRIMMER ATTACHMENT
M18 FOPH-HTA



EDGER ATTACHMENT
M18 FOPH-EA



POLE SAW ATTACHMENT
M18 FOPH-CSA



EXTENSION ATTACHMENT
M18 FOPH-EXA

QUIK-LOK™ ATTACHMENT SYSTEM

DRIVEN TO OUTPERFORM.

M18 FUEL is engineered for the most demanding tradesmen in the world. Delivering unrivaled performance in a compact structure, all M18 FUEL products feature three MILWAUKEE exclusive innovations - the POWERSTATE Brushless Motor, REDLITHIUM Battery Pack and REDLINK PLUS Intelligence Hardware and Software - that deliver unmatched power, run-time and durability.

BRUSH CUTTER ATTACHMENT
M18 FOPH - BCA



NEW

ALIGNMENT LABEL
Indicates when attachment is fully inserted into M18 FUEL Power Head

BRUSH CUTTER BLADE
4-Tooth Design

PROTECTED DRIVE SHAFT
Increased durability against drops and storage elements

BLADE GUARD
Optimized design provides enhanced material deflection

CUTTING DIAMETER 32mm (1.25”)

RUBBER BROOM ATTACHMENT
M18 FOPH - RBA



NEW

ALIGNMENT LABEL
Indicates when attachment is fully inserted into M18 FUEL Power Head

GUARD
Optimized guard design for best material containment

PROTECTED DRIVE SHAFT
Increased durability against drops and storage elements

584mm (23”) CLEARING CAPACITY

DRUM

RUBBER PADDLES
Optimized design for longer life

STRING TRIMMER ATTACHMENT
M18 FOPH - LTA



ALIGNMENT LABEL
Indicates when attachment is fully inserted into M18 FUEL Power Head

EASY LOAD TRIMMER HEAD
- Load in Under 30 Seconds
- Accepts 2mm & 2.4mm line
- Holds 7.6m of 2mm line
- Holds 6.1m of 2.4mm line

PROTECTED DRIVE SHAFT
Increased durability against drops and storage elements

350-400mm ADJUSTABLE CUTTING SWATH
- 350mm delivers maximum run-time
- 400mm maximizes clearing power and capacity

POLE SAW ATTACHMENT
M18 FOPH - CSA



ALIGNMENT LABEL
Indicates when attachment is fully inserted into M18 FUEL Power Head

PROTECTED DRIVE SHAFT
Increased durability against drops and storage elements

AUTOMATIC OILER
- 140ml Capacity
- For proper chain lubrication and increased productivity
- Translucent reservoir for clear visibility to oil levels

PADDED GRIP
- Optimal hand placement
- Delivers increased comfort

EASY ACCESS CHAIN TENSIONER
For quick adjustments to chain tension

254mm (10”) OREGON BAR & CHAIN
- Narrow Kerf Bar
- Chain Gauge: 1.1mm (.043”)
- Chain Pitch: 9.5mm (3/8”) Low Profile
- Drive Links: 40

BRANCH HOOK
For added cutting leverage and branch removal

BRISTLE BRUSH ATTACHMENT
M18 FOPH - BBA



NEW

ALIGNMENT LABEL
Indicates when attachment is fully inserted into M18 FUEL Power Head

GUARD
Optimized guard design for best material containment

PROTECTED DRIVE SHAFT
Increased durability against drops and storage elements

584mm (23”) CLEARING CAPACITY

DRUM

BRISTLE BRUSHES
Optimized design for longer life

EXTENSION ATTACHMENT
M18 FOPH - EXA



PADDED GRIP
- Optimal hand placement
- Delivers increased comfort

ADDITIONAL 940mm LENGTH

HEDGE TRIMMER ATTACHMENT
M18 FOPH - HTA



ALIGNMENT LABEL
Indicates when attachment is fully inserted into M18 FUEL Power Head

PROTECTED DRIVE SHAFT
Increased durability against drops and storage elements

PROTECTIVE GUARD
Increase users safety

25mm CUT CAPACITY

PADDED GRIP
- Optimal hand placement
- Delivers increased comfort

BLADE TIP GUARD
Prevents damage to blade and surrounding work area

ARTICULATING HEAD MECHANISM
- Adjustment handle and sliding adjustment collar allow for 270° rotation of blade set
- Delivers 13 operating positions and 1 storage position

508mm BLADE SET

EDGER ATTACHMENT
M18 FOPH - EA



ALIGNMENT LABEL
Indicates when attachment is fully inserted into M18 FUEL Power Head

PROTECTED DRIVE SHAFT
Increased durability against drops and storage elements

HIGH STRENGTH GUARD
- Metal alloy guard delivers greater durability
- Includes blade indicator mark for cut line visibility

EDGER BLADE
Industry standard 203mm blade

MUD FLAPS
Protects user from dirt and debris kickback

SKID PLATE
Protects gear box from concrete contact

ADJUSTABLE WHEEL
Optimizes blade depth and tool angle for maximum control

QUIK-LOK™ ATTACHMENT SYSTEM ACCESSORY



Shoulder Strap
49-16-2722
Designed for M18 FOPH-0



Brush Cutter Blade
49-16-2757 APJ
Designed for M18 FOPH-BCA



Trimmer Line 2mm x 45m
49-16-2712



Trimmer Line 2.4mm x 76m
49-16-2713
Designed for M18 FOPH-LTA



Easy Load Trimmer Head
49-16-2714



254mm Saw Chain
4932471329
Designed for M18 FOPH-CSA



203mm Edger Blade
4932471330
Designed for M18 FOPH-EA