

NORTON

SAINT-GOBAIN

Reshaping
your
world.



R222 - Handy Rolls

Handy Rolls Norton-R222-50x25m#180

Artical Number: 63642531807

EAN: 3157620181859



Description

R222 handy rolls are designed for manual applications. The high flexibility of the cloth in combination with the wide grit range, from coarse to fine, provides an excellent tool for a variety of applications including deburring, rust removal and finishing metal.

Features & Benefits

J-weight cloth backing

Premium aluminium oxide abrasive

Dispenser unit

Application Data

Material Application: NON-FERROUS
Machine: Manual application
Process: Sanding

Equipments:



Technical Data

| | | | |
|------------------|----------------|---------|-------|
| MarketingCAP: | R222 | Length: | |
| BackingMaterial: | Light Cotton J | Width: | 50 mm |
| Grit: | 180 | | |
| Color: | Maroon | | |
| CoatedShape: | Rolls Trimmed | | |
| CoatedSubShape: | Handyroll | | |
| | | Shape: | |

Logistic Data

| | | | |
|--------------------------|----------|----------------------------|-------------------------|
| Naked Product Weight: | 0.632 kg | Packed Product Dimension: | 180 mm x 632 mm x 60 mm |
| Naked Product Dimension: | 50x25m | pack Qty (parts per pack): | 1 pc |
| Units per part: | 1 pc | Packed Product Weight: | 1.06 kg |