

# PRODUCT SPECIFICATION

**Carl  
Kammerling**  
International

<b>Brand</b>	C.K
<b>Product Range</b>	Precision wire strippers
<b>Catalogue number</b>	3576, 3755, 3757ESD, 3757 & 3759
<b>Date</b>	13/07/2010

## Range Description

A range of precision wire strippers

## Features

- Compact design – convenient to carry
- Precision wire stripping – damage free wire preparation every time
- Depth stop adjustable up to 50mm with 1mm graduations – accurate and repeatable wire stripping
- Specially hardened blades – for a long life
- ESD version available for ESD safe areas



3756



3755



3757ESD



3757



3759 (330013)

Item Number	Item Description	EAN No	Commodity code	Carton Qty
T3756 20	Precision wire stripper for 0.2mm Diameter Wire	5013969497809	82032090	1
T3756 25	Precision wire stripper for 0.25mm Diameter Wire	5013969497908	82032090	1
T3756 30	Precision wire stripper for 0.3mm Diameter Wire	5013969498004	82032090	1
T3756 40	Precision wire stripper for 0.4mm Diameter Wire	5013969498103	82032090	1
T3756 50	Precision wire stripper for 0.5mm Diameter Wire	5013969498202	82032090	1
T3756 60	Precision wire stripper for 0.6mm Diameter Wire	5013969498301	82032090	1
T3756 80	Precision wire stripper for 0.8mm Diameter Wire	5013969498400	82032090	1
T3756 100	Precision wire stripper for 1.0mm Diameter Wire	5013969497700	82032090	1
T3757ESD 2	Precision wire stripper for 0.25 to 0.8mm Diameter Wire	5013969020434	82032090	1
T3755 018	Precision Fibre optic wire stripper for 0.18mm Diameter Cable	5013969489507	82032090	1
330009	Precision wire stripper 0.12 to 0.4mm Diameter Wire	5051073300097	82032090	1
330011	Precision wire stripper 0.3 to 1.0mm Diameter Wire	5051073300110	82032090	1
330013	Precision wire stripper for 0.25 to 0.8mm Diameter Wire	5051073300103	82032090	1

Technical product information	<b>Wire types</b> For PVC, Teflon and similar coated wires		
	<b>Wire stripping capacities</b>		
	T3756 20	mm	0.2
		awg	32
	T3756 25	mm	0.25

		awg	30					
	T3756 30	mm	0.3					
		awg	28					
	T3756 40	mm	0.4					
		awg	26					
	T3756 50	mm	0.5					
		awg	24					
	T3756 60	mm	0.6					
		awg	22					
	T3756 80	mm	0.8					
		awg	20					
	T3756 100	mm	1					
		awg	18					
	T3757ESD 2	mm	0.25	0.3	0.4	0.5	0.6	0.8
		awg	30	28	26	24	22	20
	330009	mm	0.12	0.16	0.2	0.25	0.3	0.4
		awg	36	34	32	30	28	26
	330011	mm	0.3	0.4	0.5	0.6	0.8	1
awg		28	26	24	22	20	18	
330013	mm	0.25	0.3	0.4	0.5	0.6	0.8	
	awg	30	28	26	24	22	20	
Standards compliance	None applicable							
User health and safety information	None applicable							
RoHS/WEEE compliance	These products do not fall within the scope of RoHS or WEEE regulations							
Material safety data	None applicable							
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship Damage caused through inappropriate use is not covered							
Country of origin	Germany							

## Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T3756 20	98	10	54	24	98	10	54	25
T3756 25	98	10	54	24	98	10	54	25
T3756 30	98	10	54	24	98	10	54	25
T3756 40	98	10	54	24	98	10	54	25
T3756 50	98	10	54	24	98	10	54	25
T3756 60	98	10	54	24	98	10	54	25
T3756 80	98	10	54	24	98	10	54	25

T3756 100	98	10	54	24	98	10	54	25
T3757ESD 2	98	10	54	26	98	10	54	27
T3755 018	98	10	54	26	98	10	54	27
330009	98	10	54	26	98	10	54	27
330011	98	10	54	26	98	10	54	27
330013	98	10	54	26	98	10	54	27

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T3756 20	-	-	-	-		
T3756 25	-	-	-	-		
T3756 30	-	-	-	-		
T3756 40	-	-	-	-		
T3756 50	-	-	-	-		
T3756 60	-	-	-	-		
T3756 80	-	-	-	-		
T3756 100	-	-	-	-		
T3757ESD 2	-	-	-	-		
T3755 018	-	-	-	-		
330009	-	-	-	-		
330011	-	-	-	-		
330013	-	-	-	-		

### Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T3756 20	1	Bag						
T3756 25	1	Bag						
T3756 30	1	Bag						
T3756 40	1	Bag						
T3756 50	1	Bag						
T3756 60	1	Bag						
T3756 80	1	Bag						
T3756 100	1	Bag						
T3757ESD 2	1	Bag						

T3755 018	1	Bag						
330009	1	Bag						
330011	1	Bag						
330013	1	Bag						