



ENGLISH

## Datasheet

# RS Pro All Purpose High Tack Duct Tape

Stock No: 146-6829

### General Description

A polycloth laminate waterproof gloss cloth tape coated with an aggressive pressure sensitive, solvent free rubber-resin adhesive

- Very high tack, instant grab
- Easy tear
- Consistent unwind
- Good abrasion resistance
- Water resistant finish
- Conformable to awkward shapes
- Non-corrosive adhesive

### Technical Details

#### Typical Values

Thickness	0.17mm
Breaking Load	35 N/cm
Elongation	18%
Adhesion	
Steel	4.0 N/cm
Self	3.0 N/cm
RoHS Compliant	Yes
Service Temperature	-50°C to +65°C
Application Temperature	+5°C to +45°C
Storage Temperature	+12°C to +25°C

#### STORAGE

Tapes stored below the minimum recommended temperature will require warming up to that level before use. Up to 24 hours may be required for this to take place.