

FEATURES

- **Nylon Material:** Provides durability and resistance to wear and tear
- **UV Resistant:** Suitable for outdoor applications, preventing degradation from sunlight
- **Length of 940 mm:** Accommodates large bundles, offering flexibility in various applications
- **Maximum Bundle Diameter of 284 mm:** Ensures compatibility with a wide range of cable sizes
- **Tensile Strength of 80 kg:** Offers robust support for heavy-duty applications
- **Fire Behaviour UL 94 V-2:** Provides a level of flame retardancy for safety
- **Maximum Operating Temperature of 85 °C:** Suitable for use in high-temperature environments

RS PRO Heavy Duty Cable Tie, Nylon 940 mm

RS Stock No: 656-064



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO Heavy Duty Cable Tie is designed for securing and organising cables in demanding environments. Made from durable nylon, it offers a reliable solution for managing large bundles of cables, ensuring they remain tidy and secure. Ideal for industrial applications, this cable tie provides strength and UV resistance, making it suitable for both indoor and outdoor use.

General Specifications

Colour	Natural
Product Type	Cable Tie
Sub Type	Heavy Duty Cable Tie
Tensile Strength	80 kg

Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	Yes

Mechanical Specifications

Length	940 mm
Material	Nylon
Maximum Bundle Diameter	284 mm
Width	9 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, CE 40022513, cULus E97527, DNV TAE00000US, LR 16-80006, RoHS, UL94V-2, VDE 40022513
---------------------	---