



ENGLISH

Datasheet

Stock No. 184-5570

RS PRO Capacitive Sensor



Specifications:

Mounting: Flush
Rated distance Sn: 5mm(Adjustable)
Assured distance Sa: 0...4mm
Shape size: 30*50*7mm
Output way: PNP
Output status: NO
Supply voltage: 10...30 VDC
Standard target: Fe15*15*1t
Switch point offset[%/Sr]: $\leq \pm 20\%$
Hysteresis range [%/Sr]: 3...20%
Repeated error: $\leq 3\%$
Load current: $\leq 200\text{mA}$
Residual voltage: $\leq 2.5\text{V}$
Current consumption: $\leq 15\text{mA}$
Protection circuit: Reverse polarity protection
Output indicator: Yellow LED
Ambient temperature: $-10^{\circ}\text{C} \dots 55^{\circ}\text{C}$
Ambient humidity: 35-95%RH
Switch frequency: 60 Hz
High pressure resistance: 1000V/AC 50/60Hz 60s
Insulation resistance: $\geq 50\text{M}\Omega(500\text{VDC})$
Vibration resistance: Complex amplitude 1.5mm 10...50Hz(2H per X,Y,Z direction)
Protection degree: IP67
Housing material: PBT
Connection: 2m PVC cable

Features:

- ◆ Be able to detect both metal and nonmetal objects;
- ◆ Be able to detect various media via nonmetallic container;
- ◆ Reliable liquid level detecting;

25/3/2019