



PRODUCT DATASHEET

Datasheet creation date: 2025/05/28 7:43 (UTC)



6000

Single-Row Deep Groove Ball Bearings

Boundary Dimensions

d	10	mm	Bore diameter
D	26	mm	Outside diameter
B	8	mm	Width
r (min.)	0.3	mm	Chamfer dimension

Basic Load Ratings

Cr	5050	N	Basic dynamic load rating
C0r	1970	N	Basic static load rating

Speeds

Grease	30000	min-1	Grease lubrication
Oil (Oil-bath)	36000	min-1	Oil-bath lubrication

Abutment and Fillet Dimensions

da (min.)	12	mm	Diameter of shaft abutment
da (max.)	13	mm	Diameter of shaft abutment
Da (max.)	24	mm	Diameter of housing abutment
ra (max.)	0.3	mm	Radius of shaft or housing fillet

Calculation factors

fo	12.4		Factor
----	------	--	--------

Additional information

z	7		Number of Balls
Dw	4.762	mm	Ball Diameter

Mass

Mass approx.	0.018	kg	Mass approx.
--------------	-------	----	--------------

