



Pneumatic ratchet wrench 3/8" 122nm

1014100A

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 08:49:21





DESCRIPTION

Pneumatic ratchet wrench 3/8" 122nm

COMFORTABLE

Upper and lower support stop on the handle for an excellent grip. Agreeable elastomer handle.

RELIABLE

Its power/low speed ratio makes it possible to ensure delicate tightening without deteriorating the assembly.

The 3/8" ratchet wrench is perfect for users who prefer composite material tools. It provides a comfortable grip, light weight and insulation against the cold.

Reversible 3/8" wrench designed for maintenance operations.

Long control lever for optimum flow setting. Exhaust to the rear.

STANDARDS / DIRECTIVES

2006/42/CE, ISO 15744

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 08:49:21



SPECIFIC DATA

Designation	RATCHET WRENCH 3/8" 122 NM
Sales reference	1014100A
L (mm)	245
Weight (g)	1330
l (mm)	41
H (mm)	53
drive square	3/8"
Rotation speed (rpm)	160
Vibration (m/s ²)	4.7
Noise level (dBa)	93
C mm	6.3
C min mm	1/4"
C mm	122
Maximum input torque Nm	
Guarantee	M2 SAM Equipment and Machine Guarantee

Guarantee applied

M2 | SAM Equipment and Machine Guarantee

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

[>> Find out more](#)

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

