

XEVOX DUPLEX MW VDS Motion Detector

BW8030



Specifications			
Installation	Wall	Detection method	PIR / MW
Detection range (m)	15 x 15	Alarm memory	Yes
Immune to animals	No	Power consumption	13 mA
Voltage supply	9 –16 V	Alarm contact	NC, 50 mA, 24 V DC
Tamper contact	NC, 100 mA, 24 V DC	Temperature range	–10° to 55 °C
VDS	G106509	VSÖ	GS–N060614/05E