



Oil



Light Duty

Highly durable oil-repellent gloves, protecting hands with dexterous comfort

- **Specialized protection:** HyFlex® 11-917 light-duty industrial gloves feature dipped nitrile coating, guarding against liquid, oil, grease and dirt
- **Improved durability:** Their nitrile coating also ensures durability and longer wear life, satisfying advanced EN-compliant abrasion resistance standards
- **Elevated comfort:** A seamless nylon liner helps ensure these liquid-repellent safety gloves are both dexterous and comfortable
- **Food handling compliance:** These HyFlex® gloves are also suitable for various food processing applications
- **Minimized health risks:** They are DMF-free and certified by Oeko-Tex® as free of substances harmful to human health



Industries

- Agriculture
- Machinery and Equipment
- Construction
- Food Processing

Applications

- Assembly of white goods
- Maintenance
- Preparation of site - unloading of lines and valves
- Metal Fabrication
- Quality control

Key Features

- **Liquid-repellent design:** Protection from liquid, oil, grease and dirt
- **Dipped nitrile coating:** Excellent abrasion resistance levels
- **Seamless nylon liner:** Optimized fit, boosting comfort and dexterity

Vulcanization Chemical Accelerators

- Natural rubber proteins (in knitwrist elastic)
- Zinc Dibutyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Technologies



DMF free



Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-917	Finishing: Dipped Coating Material: Nitrile Liner Material: Nylon Cuff Style: Knitwrist	13	6, 7, 8, 9, 10, 11	225-280 mm	Blue	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699