

### A622 - MR Cut PU Palm Glove

**Collection:** Cut Resistant

**Range:** Gloves

**Materials:** HPPE, Elastane, Glass Fibre, Elastic, Polyester

**Inner Pack:** 12

**Outer Carton:** 144

### Product information

Level C cut resistant glove for protection against cuts and sharp objects. Seamless liner for added comfort and dexterity. EN407 contact heat level 1 provides short term protection against temperatures up to 100°C

### Gloves

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwest's extensive range of Hand Protection products....

### Standards

EN ISO 21420 Dexterity 5

EN388:2016 +A1:2018 - (4X43C)

EN 407 (X1XXXX)

ANSI/ISEA 105: 2016 Type A (A3)



### Features

- Level C cut resistance
- 13 gauge liner for a perfect fit
- Smooth PU coating for increased abrasion resistance
- Palm dipped to increase dexterity and ventilation
- Breathable seamless liner
- Medium risk cut protection
- CE certified
- Retail tag which aids presentation for retail sales
- ANSI cut level A3
- Superb abrasion and tear resistance

# PORTWEST®

## PRODUCT SPECIFICATION & TECHNICAL DATA

### A622 - MR Cut PU Palm Glove Commodity Code: 6116108000

#### Test House

Cert No: 0075/2085/162/12/19/3530

#### CARTON DIMENSIONS/WEIGHT

Item	Colour	Len	Wid	Hgt	Weight (Kg)	Cubic (m <sup>3</sup> )	EAN13	DUN14
A622G7RXS	Grey	51.0	30.0	43.0	0.0690	0.0658	5036108273874	15036108786876
A622G7RS	Grey	51.0	30.0	43.0	0.0700	0.0658	5036108217083	15036108704269
A622G7RM	Grey	51.0	30.0	43.0	0.0710	0.0658	5036108217076	15036108704252
A622G7RL	Grey	51.0	30.0	43.0	0.0720	0.0658	5036108217069	15036108704245
A622G7RXL	Grey	51.0	30.0	43.0	0.0750	0.0658	5036108217090	15036108704276
A622G7RXXL	Grey	51.0	30.0	43.0	0.0610	0.0658	5036108217106	15036108704283
A622G7RXXXL	Grey	51.0	30.0	43.0	0.0850	0.0658	5036108292530	15036108782434