

PREVOST FILTRATION - SINGLE UNITS

Electrically operated pressure relief valve



Part number	Female thread	Flow rate at 6.00 bar (l/min) ($\Delta P = 1.00$ bar)	Temperature min/max (°C)	Max. operating pressure (bar)	Net weight (Kg)
ATU E100	G1/8	1500.00	5.00 / 50.00	10.00	0,369
ATU E101	G1/4	3000.00	5.00 / 50.00	10.00	0,369
ATU E102	G3/8	6400.00	5.00 / 50.00	10.00	0,776
ATU E103	G1/2	9000.00	5.00 / 50.00	10.00	0,776

