

Laser Measures

Features

- Record up to 20 points of reference without having to move back-and-forth
- Fairly lightweight, pocket-sized digital measure
- Automatic shutdown build-in function after inactivity of 3 minutes
- Determination of the maximum and minimum values feature
- Addition and subtraction of indications
- Laser pointer targets to avoid costly mistakes
- LCD status indicator
- Rating of IP 54, giving you protection against dust ingress
- Offers standard distance calculator to help you make a formal decision
- Indirect Measurement Using Tilt Sensor
- Bluetooth with APP Support (Meterbox Pro)

RS PRO ILDM-150H Laser Measure, 0.05 → 70m Range, ± 1.5 mm Accuracy

RS Stock No: 126-8822



RS PRO Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Laser Measures

Product Description

A conventional tape measure is reliable, but an old school source of information. To save time, money and put accuracy to the next level, you need a reliable measurement to keep up with your increasing requirements.

We are proudly introducing our own branded RS PRO LCD Measure Meters distance where only one hand is occupied while using the device, instead of two while using traditional tape. You are getting quick, non-contact measurement figures for height, distance or angles in seconds, so you can focus on other small or big tasks.

General Specifications

Accuracy	± 1.5 mm
Measurement Range	0.05 → 70m
Imperial or Metric	Imperial, Metric
Display Type	LCD
Laser Class	Class 2
Laser Wavelength	635nm
Battery Life	up to 8000
Power Source	Battery
Weight	203g
Model Number p	ILDm-150H