



Portable Hard Drives  
**StoreJet 25M3**

Transcend's StoreJet 25M3 ruggedized portable hard drive combines supreme shock-resistant qualities with the USB 3.1 Gen 1 interface, allowing for ultra-fast file transfers and the highest level of anti-shock protection.



**Rugged and portable**

The StoreJet 25M3 portable hard drive was designed with high endurance in mind, allowing you to store and share wherever you go. Two color options, iron gray and military green, make for a stylish, trendy storage experience!



**Excellent anti-shock protection**

The StoreJet 25M3 features a three-stage shock protection system that has passed MIL-STD-810G US military transit drop test to fully protect data stored on the drive. The three-stage shock protection system includes a silicone rubber case, an internal shock-absorbing suspension damper, and a reinforced hard casing.



**USB Type-A supported. Durable and reliable.**

The StoreJet 25M3 portable hard drive utilizes a USB Type-A connector that has undergone 10K plug-unplug tests. High durability means extra protection for your files.



## Portable Hard Drives StoreJet 25M3

### Features

- USB 3.1 Gen 1 interface
- Three-stage shock protection system that meets US military drop-test standards
- Convenient one-touch auto-backup for instant data backup
- Up to 4TB storage capacity
- Ruggedized and reliable



**Transcend Elite**

Transcend Elite is a data management software for external hard drives, USB flash drives and portable SSD products.



**RecoverRx**

RecoverRx is a data recovery software for memory cards, USB flash drives, external hard drives and SSDs.

### Specifications

#### Appearance

Dimensions	1TB/2TB: 129.5 mm x 80.8 mm x 16.1 mm (5.10" x 3.18" x 0.63") 4TB: 129.5 mm x 80.8 mm x 24.1 mm (5.10" x 3.18" x 0.95")
Weight	1TB/2TB: 185 g (6.53 oz) 4TB: 294 g (10.37 oz)
Color	Iron gray / Military green

#### Interface

USB Type	micro USB to USB Type A
Connection Interface	USB 3.1 Gen 1

#### Storage

Capacity	1 TB / 2 TB / 4 TB
Storage Media	2.5" HDD

#### Operating Environment

Operating Temperature	5°C (41°F) ~ 55°C (131°F)
Operating Voltage	5V

#### Warranty

Certificate	CE / FCC / BSMI / KC / RCM / EAC
Warranty	Three-year Limited Warranty

### Ordering Information

1TB	TS1TSJ25M3G TS1TSJ25M3S
2TB	TS2TSJ25M3G TS2TSJ25M3S
4TB	TS4TSJ25M3S

Product specifications are subject to change without notice. Pictures shown may differ from actual products. Total accessible capacity varies depending on operating environment.