

#BEGREENBESEEN



## FEATURES

Naturally renewable, biodegradable, absorbent and wicking; keeping you dry with reduced wash frequency; super soft, ideal for sensitive skin.

Heat applied 50 wash stretchy segmented reflective tape.

Fresche anti-bacterial treatment, reduces bad odours, thus helping to reduce the need to wash the garment when not dirty.

Bamboo and natural fibre next to the skin with 80% bamboo, 13% recycled polyester and 7% elastane blend collar.

Extended body length.

The fabric naturally provides Ultraviolet Protection Factor rating of 40+, offering maximum protection against the dangers of harmful UV rays.

Green PULSAR® and LIFE branding, with Green PULSAR® branded buttons made of 47% recycled post-consumer polyester and 53% polyester.

## SPECIFICATIONS

CODE: **LFE923-NB - Yellow** **LFE924-NB - Orange**

MEN'S SIZE OPTIONS: S-6XL

CODE: **LFE973-NB - Yellow** **LFE974-NB - Orange**

WOMEN'S SIZE OPTIONS: 8-26

FABRIC: 160gsm 60% GRS recycled polyester, 40% bamboo knitted pique

### Limitations of use, Warning of Misuse - EN 13758-2

Garments must be worn fastened. Should the high visibility properties of garments become seriously impaired this item should be replaced. **Warning:** Sun exposure causes skin damage.

Only covered areas offer UVA and UVB protection from the sun. The protection offered by this garment may be reduced, with use, if stretched, or when wet.

## AFTERCARE

Do not wash in biological powder, wash as synthetics.

Maximum 50 domestic wash cycles.

40°C domestic wash only, hang dry, do not iron.

Do not tumble dry, do not dry clean, do not use bleach.

Do not use fabric softener.



## STANDARDS



EN ISO 20471  
Class 2



RIS-3279 Rail Standard  
(Orange styles only)



EN 13758-2  
40+

## QUICK SIZE GUIDE (TO FIT CHEST)

XS 31" - 34"	S 34" - 37"	M 37" - 40"
L 40" - 43"	XL 43" - 46"	2XL 46" - 50"
3XL 50" - 55"	4XL 55" - 59"	5XL 59" - 63"
6XL 63" - 66"	7XL 66" - 70"	

## QUICK SIZE GUIDE (TO FIT CHEST)

8 29" - 32"	10 32" - 34"	12 34" - 37"
14 37" - 39"	16 39" - 41"	18 41" - 43"
20 43" - 45"	22 45" - 47"	24 47" - 49"
26 49" - 52"		