

FEATURES

- Metric hex nuts
- To DIN934
- A4 grade 18/8 stainless steel (Type 316 S16) – long lasting
- Good resistance to corrosion and saltwater
- Easy to tighten and loosen

RS PRO Stainless Steel Hex Nut, Plain, M8

RS Stock No.: 189-608



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO A4 stainless steel hex nuts ideal for use in chemical processing equipment and marine environments due to its higher resistance to tarnish and corrosion. These nuts are the most common hexagonal fastener that has internal threads that screw on to the shank of a bolt or a hex cap screw. These RS PRO hex nut fasteners come in various thread sizes:

- 248-4551 – M2
- 248-4567 – M2.5
- 189-563 – M3
- 189-579 – M4
- 189-585 – M5
- 189-591 – M6
- 189-608 – M8
- 189-614 – M10
- 183-9045 – M12
- 248-4573 – M16
- 248-4589 – M20

General Specifications

Thread Size	M8
Material	Stainless Steel
Type	Full
Finish	Plain
Applications	Chemical processing equipment, Marine Environments, Automotive Applications, Construction Industry, General Industry, Machinery, Workshops

Mechanical Specifications

Width	13mm
Stainless Steel Type	316 A4
Specification	DIN 934, ISO 4032
Thickness	6.44mm to 6.8mm
Thread Pitch	1.25mm
Width Across Corners	14.38mm
Width Across Flats	12.73mm to 13mm

