

TORQUE WRENCH SET 3/8 1/2IN DR 2PCS

Item ID: TEX1238



Length (mm):	52
Width (mm):	119
Height (mm):	581
Weight (kg):	2.717

- 2 piece angular gauge torque wrench set
- Includes 3/8" and 1/2" drive torque wrenches giving a range of 10 to 210Nm
- Each torque wrench is equipped with an in-built angular gauge for easier after tightening of stretch bolts (TTY torque to yield fasteners)
- Click type mechanism with easily recognisable signal when the required torque is reached
- Simple to adjust and easy to read Nm scale
- Additional ft/lb reference scale (range 4-18 ft/lb)
- Clearly marked with three bands to show the correct place on the handle where pressure should be applied to give a more accurate torque reading
- Twist locking facility to ensure the set torque is maintained
- Reversible 24 teeth ratchet mechanism (DIN3122) giving 15° increments for strength and for added reference when torquing stretch bolts
- Designed to torque right hand (clockwise) fasteners
- Accurate to +/- 4% and conforms to ISO6789 for assured reliability and accuracy
- Individually tested and certified at the time of manufacture
- Each torque wrench has it's own individual certification number for easier quality control management
- Supplied in the unique Teng Tools drawer width TTX tray
- Use on it's own or as part of the Teng Tools "Get Organised" system
- Tools are held in place using three colour pre-cut EVA foam clearly showing where each tool belongs
- Designed and manufactured to ISO6789

Technical changes and errors may occur

WWW.TENGOOLS.COM



Get organised™