

BIZ1 - Bizweld Work FR Coverall

Collection: Bizweld™ Work

Range: Flame Resistant Multi-Norm

Shell Fabric: Bizweld Work: 100% Cotton, 330g

Outer Carton: 12

Product information

Voted the number one favourite coverall in the welding industry, our best selling Bizweld coverall is ideal for offering complete protection to workers exposed to heat. The generous fit provides comfort and allows the wearer to work unhindered whilst ample storage space, rule pocket and concealed mobile phone pocket hold equipment securely and safely.

Bizweld™ Work

Bizweld™ Work protective clothing have been specially designed to guarantee comfort, performance and safety whilst providing effective function at all times. Bizweld™ Work has been rigorously tested to ensure total compliance with the latest international standards.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, E2, F1)

EN ISO 11611 Class 1 (A1+A2)

IEC 61482-2 IEC 61482-1-1 (ELIM 8.3 CAL/CM², ATPV 10.9 CAL/CM²)

ASTM F1959/F1959M-12 (ATPV 11.2 CAL/CM² (HAF = 80.4%))



Features

- Protection against radiant, convective and contact heat
- Certified protection against molten metal splash
- Concealed stud front for easy access
- Chest pockets with stud closure
- Stud adjustable cuffs for a secure fit
- Rule pocket
- Radio loop for easy clipping of a radio
- Concealed phone pocket
- 6 pockets for ample storage
- CE-CAT III
- CE certified

BIZ1 - Bizweld Work FR Coverall

Commodity Code: 6211321000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)

Bracetown Business Park

D15 YN2P, Ireland

Cert No: 2777/12872-03/E00-00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
BIZ1RERXS	Red	43.0	28.0	52.0	1.2500	0.0626	5036108245406	25036108731835
BIZ1RERS	Red	43.0	28.0	52.0	1.2200	0.0626	5036108059140	25036108607628
BIZ1RERM	Red	43.0	28.0	52.0	1.2900	0.0626	5036108059157	25036108607611
BIZ1RERL	Red	43.0	28.0	58.0	1.2900	0.0698	5036108059164	25036108607604
BIZ1RERXL	Red	43.0	28.0	58.0	1.3900	0.0698	5036108059171	25036108607635
BIZ1RERXXL	Red	43.0	28.0	58.0	1.4200	0.0698	5036108059188	25036108607642
BIZ1RERXXXL	Red	43.0	28.0	58.0	1.4000	0.0698	5036108059195	25036108607659
BIZ1RER4XL	Red	43.0	28.0	58.0	1.5600	0.0698	5036108059201	25036108703597
BIZ1RER5XL	Red	43.0	28.0	58.0	1.6200	0.0698	5036108216468	25036108703603