



ENGLISH

Datasheet

RS Pro SYSCAL(255550)TYPE K SURFACE METER

RS Stock No: **287-024**

Product Details

RS Pro surface meter is a k type meter.

Features and Benefits

- K type

**Specifications:**

Best Accuracy	±0.25%
Cable Length	2 m
Calibrated	SYSCAL
Connector Type	Miniature Plug
Maximum Temperature Measurement	+180°C
Probe Diameter	60 mm
Probe Length	110 mm
Probe Tip Type	Bow
Probe Type	Surface
Sensor Type	K
Ambient Temperature	-30 to +50°C
Minimum Temperature Measurement	-50°C
Response Time	10 s